



General Specifications

Supply Input.....	+9V to 30V 2A <i>Examples:</i> Digikey part 102-1337-ND or 62-1047-ND (enclosed)
Dimensions.....	1.6" X 1.6" (40mm X 40mm) square, .687" (17.45mm) thick
Operating Modes.....	PC controlled or standalone
PC Control.....	Can control up to 16 EZcontrollers daisy chained together.
Communications Protocol.....	RS485. Can convert to RS232/USB with appropriate converter. Provision is made for future addition of CAN bus protocol.
Control Protocol.....	Compatible with devices that use the Cervo DT or OEM protocol. Can use EZCommander™ Windows application or serial terminal program such as HyperTerminal to issue commands.
Mating Connectors	AMP MTA 100 series. Recommended tools: Digikey A9982; or A1998 + A2031. (See Application Note 131021 for non-standard connector options.)
ADC and Encoder Inputs.....	Signal Levels: <0.8V Vlow; >2V Vhigh (TTL compatible). Accurate to 8 bits; can be modified for 10-bit accuracy (details available).
Optical switches	Transistor optical switch with IC > 1 mA @ IF=20mA. <i>Examples:</i> Digikey QVA11134 or H21A1; Honeywell HOA1887-012 or HOA1870-33 (prewired); OPTEK OPB830W11 (prewired)
Operating Temperature.....	-20 to 85 °C PCB copper temperature
Relative Humidity.....	10% to 90% non condensing (operating and storage)

INPUT CONNECTOR

Mating connector: AMP MTA 100 Series 8 pin, 26 GA, part 3-643815-8
Digikey part A31030-ND

Pin	Function	Notes
1	Switch input #2, A/D input #2, Encoder #2 Chan B, Dir In	Includes 10k Ω pullup to 3.3V.
2	Switch input #1, A/D input #1, Encoder #2 Chan A, Step In	Includes 10k Ω pullup to 3.3V.
3	Opto sensor #2 LED	Includes series 200 Ω resistor to 5V. Resistor can be removed for applications that require direct access to 5V.
4	Opto sensor #2, A/D input #4, Encoder #2 Index	Includes 10k Ω pullup to 3.3V.
5	Opto Sensor #2 ground	Common input ground
6	Opto Sensor #1 LED	Includes series 200 Ω resistor to 5V. Resistor can be removed for applications that require direct access to 5V.
7	Opto Sensor #1 input, A/D input #3	Includes 10k Ω pullup to 3.3V.
8	Opto sensor #1 ground	Common input ground

CONTROL OUTPUT CONNECTORS (AXIS 1 THROUGH 4)

Mating connector: AMP MTA 100 Series 5 pin, 22 GA, part 3-643813-5
Digikey part A31027-ND

Pin	Function	Notes
1	V+ 9V to 30V	Power output
2	Power ground	Power return
3	Step out	Open collector to ground. Pulse output
4	Direction out	Open collector to ground. Voltage level output
5	Axis Home Input	


ENCODER CONNECTOR

Mating connector: AMP MTA 100 Series 5 pin, 26 GA, part 3-643815-5
Digikey part A31027-ND

Pin	Function	Notes
1	Ground	Ground for encoder
2	Index 1	Input from encoder
3	Chan A	Input from encoder
4	+5V (V+)	Power to encoder
5	Chan B	Input from encoder



4-axis stepper motor controller



Model EZCTRL17-ST actual size

Rapidly configurable, fully intelligent 4-axis stepper control with two opto-electronic/mechanical switch inputs, up to 8 (configurable) analog-to-digital (A/D) converter inputs, and step/direction outputs compatible with most stepper motor driver amplifiers

POWER AND RS485 CONNECTOR

Mating connector: AMP MTA 100 Series 4 pin, 22 GA, part 3-643813-4
Digikey part A31108-ND


Pin	Function
1	V+ (external supply) +9V to 30V
2	Ground
3	RS485 B
4	RS485 A

CAN CONNECTOR

Mating connector: AMP MTA 100 Series 2 pin, 22 GA, part 3-643813-2
Digikey part A31107-ND

Pin	Function	Notes
1	CAN High	Not active at this time
2	CAN Low	Not active at this time

Connector Locations




Key Features

- 4-axis stepper motor controller
- +9V to 30V operation
- Pre-wired for opto-switch inputs
- RS232, RS485, or USB-based communications
- Single 4-wire bus linking up to 16 controllers
- Switch-selectable device address
- Industry standard communications protocol
- Standalone operation with no connection to a PC
- Pulse output for step and voltage level for direction are accepted by most stepper motor amplifiers
- Dual encoder readback (optional encoder feedback)
- Execution Halt pending switch closure
- Homing to opto or switch closure with one command
- Fully programmable ramps and speeds

Mechanical Specifications

4-axis stepper motor controller



Ordering Information

Name	Order Number
3-axis stepper motor controller.....	EZCTRL17-ST
RS232 to 485 Converter (option).....	RS485
USB to 485 Converter (option).....	USB485